

# FBI 3- 8 - Fixed bridge

0200059

<https://www.phoenixcontact.com/us/products/0200059>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fixed bridge, pitch: 8 mm, number of positions: 3, color: silver-colored



## Commercial data

Item number	0200059
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918253547
Weight per piece (including packing)	7.74 g
Weight per piece (excluding packing)	7.74 g
Customs tariff number	85369095
Country of origin	CN

# FBI 3- 8 - Fixed bridge



0200059

<https://www.phoenixcontact.com/us/products/0200059>

## Technical data

### Product properties

Product type	Screw bridge
Number of positions	3
Pitch	8 mm

### Dimensions

Pitch	8 mm
-------	------

### Material specifications

Color	silver-colored
Material	Copper
Insulating material	PA

### Mounting

Mounting type	Screw mounting
---------------	----------------

# FBI 3- 8 - Fixed bridge



0200059

<https://www.phoenixcontact.com/us/products/0200059>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 10.0	EC000489
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FBI 3- 8 - Fixed bridge



0200059

<https://www.phoenixcontact.com/us/products/0200059>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)