

FB 100- 6 - Fixed bridge



0201524

<https://www.phoenixcontact.com/us/products/0201524>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fixed bridge, pitch: 6.2 mm, number of positions: 100, color: silver-colored

Commercial data

Item number	0201524
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918252076
Weight per piece (including packing)	159.52 g
Weight per piece (excluding packing)	159.188 g
Customs tariff number	85389099
Country of origin	DE

FB 100- 6 - Fixed bridge



0201524

<https://www.phoenixcontact.com/us/products/0201524>

Technical data

Product properties

Product type	Screw bridge
Number of positions	100
Pitch	6.2 mm

Dimensions

Pitch	6.2 mm
-------	--------

Material specifications

Color	silver-colored
Material	Copper
Coating	tin-plated

Mounting

Mounting type	Screw mounting
---------------	----------------

FB 100- 6 - Fixed bridge



0201524

<https://www.phoenixcontact.com/us/products/0201524>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com