

EB 100- 6 - Insertion bridge



0201993

<https://www.phoenixcontact.com/us/products/0201993>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, not insulated, pitch: 6.2 mm, number of positions: 100, length: 616 mm, color: silver/matt

Commercial data

Item number	0201993
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918245443
Weight per piece (including packing)	51.3 g
Weight per piece (excluding packing)	49.5 g
Customs tariff number	85366990
Country of origin	DE

EB 100- 6 - Insertion bridge



0201993

<https://www.phoenixcontact.com/us/products/0201993>

Technical data

Product properties

Product type	Insertion bridge
Number of positions	100
Pitch	6.2 mm
Potentials	100

Dimensions

Width	1 mm
Height	19.8 mm
Length	616 mm
Pitch	6.2 mm

Material specifications

Color	silver/matt
Material	CuZn (nickel-plated)
Insulating material	PA

Mounting

Mounting type	Screw mounting
---------------	----------------

EB 100- 6 - Insertion bridge

0201993

<https://www.phoenixcontact.com/us/products/0201993>



Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EB 100- 6 - Insertion bridge



0201993

<https://www.phoenixcontact.com/us/products/0201993>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com