

# FBI 3- 6 M.MONTIERTEN SCHRAUB - Fixed bridge



0203357

<https://www.phoenixcontact.com/us/products/0203357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fixed bridge, pitch: 6 mm, number of positions: 3, color: silver-colored



## Commercial data

Item number	0203357
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918253707
Weight per piece (including packing)	4.978 g
Weight per piece (excluding packing)	4.763 g
Customs tariff number	85369095
Country of origin	DE

# FBI 3- 6 M.MONTIERTEN SCHRAUB - Fixed bridge



0203357

<https://www.phoenixcontact.com/us/products/0203357>

## Technical data

### Product properties

Product type	Screw bridge
Number of positions	3
Pitch	6 mm

### Dimensions

Pitch	6 mm
-------	------

### Material specifications

Color	silver-colored
Material	Copper
Insulating material	PA

### Mounting

Mounting type	Screw mounting
---------------	----------------

# FBI 3- 6 M.MONTIERTEN SCHRAUB - Fixed bridge



0203357

<https://www.phoenixcontact.com/us/products/0203357>

## Classifications

### UNSPSC

UNSPSC 21.0	39121426
-------------	----------

# FBI 3- 6 M.MONTIERTEN SCHRAUB - Fixed bridge



0203357

<https://www.phoenixcontact.com/us/products/0203357>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)