TSS-RTK-BEN - Insulation plate

0309219

https://www.phoenixcontact.com/us/products/0309219

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Special separating plate

Commercial data

Item number	0309219
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE1Z1X
GTIN	4017918320492
Weight per piece (including packing)	3.672 g
Weight per piece (excluding packing)	3.937 g
Country of origin	DE

Technical data

Product properties

Product type	Divider plate

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

Dimensions

Width	0.8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com