

# EK 116 - Power terminal block



0401010

<https://www.phoenixcontact.com/us/products/0401010>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power terminal block, connection method: Screw connection, Rated cross section: 10 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup> - 16 mm<sup>2</sup>, mounting: Neutral busbar, color: aluminum color

## Commercial data

Item number	0401010
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE73
Product key	BE7331
GTIN	4017918001766
Weight per piece (including packing)	28.87 g
Weight per piece (excluding packing)	28.5 g
Customs tariff number	85369010
Country of origin	PL

## Technical data

### Product properties

Product type	Pick-off terminal
Number of connections	1
Number of rows	1

### Electrical properties

Maximum load current	76 A (with 16 mm <sup>2</sup> conductor cross-section)
Nominal current I <sub>N</sub>	57 A
Current carrying capacity of the neutral busbar	140 A

### Connection data

Nominal cross section	10 mm <sup>2</sup>
Maximum load current	76 A (with 16 mm <sup>2</sup> conductor cross-section)

#### Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M5
Tightening torque	1.7 ... 2 Nm
Stripping length	14 mm
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	20 ... 8 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
2 conductors with same cross section, flexible	0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Nominal cross section	10 mm <sup>2</sup>

### Ex data

#### Rated data (ATEX/IECEx)

Torque range for mounting screw	1.7 Nm ... 2 Nm
---------------------------------	-----------------

### Dimensions

Width	8 mm
Height	36 mm
Length	40 mm

### Material specifications

Color	aluminum color
-------	----------------

### Mounting

Mounting type	Neutral busbar
---------------	----------------

# EK 116 - Power terminal block



0401010

<https://www.phoenixcontact.com/us/products/0401010>

## Classifications

### UNSPSC

UNSPSC 21.0

39121426

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)