PMH 0:UNBEDRUCKT - Wire marking tag

0800417

https://www.phoenixcontact.com/us/products/0800417

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, yellow (RAL 1018), cable diameter range: 1.4 ... 2.5 mm: without print, mounting type: slide-on, text field height: 2.6 mm, text field width: 3.2 mm

Commercial data

Item number	0800417
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG17
Product key	BG221B
GTIN	4017918005979
Weight per piece (including packing)	0.074 g
Weight per piece (excluding packing)	0.064 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Product properties

Product type	Conductor marker

Marking

Printing	without print

Dimensions

Width	3.2 mm
Length	4.5 mm

Text field

Text field width	3.2 mm
Text field height	2.6 mm

Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	1.4 mm ... 2.5 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-45 °C ... 70 °C

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	slide-on

Classifications

ECLASS

ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com