
PMH 2:GROSSBUCHSTABEN - Wire marking tag

0800514

https://www.phoenixcontact.com/us/products/0800514

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a combination of upper case letters, symbols and figures in versions PMH -0, -2 and -4

Wire marking tag, yellow (RAL 1018), cable diameter range: 3 ... 6 mm, horizontal: Letters, mounting type: slide-on, text field height: 2. 6 mm, text field width: 4.2 mm

Commercial data

Item number	0800514
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	NULL
Product key	BG222B
Weight per piece (including packing)	295 mg
Weight per piece (excluding packing)	295 mg
Customs tariff number	49119900
Country of origin	CZ

Technical data

Notes

General	Please specify the required marking with order: Minimum order per imprint: 1 packing unit

Product properties

Product type	Conductor marker

Marking

Printing direction	horizontal
Printing	Letters

Dimensions

Width	4.2 mm
Height	9.5 mm
Length	6.6 mm

Text field

Text field width	4.2 mm
Text field height	2.6 mm

Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	3 mm ... 6 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-45 °C ... 70 °C

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	slide-on

Classifications

ECLASS

ECLASS-13.0	27281102

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com