

# PMH 2:GROSSBUCHSTABEN B - Wire marking tag



0800514:B

<https://www.phoenixcontact.com/us/products/0800514:B>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the capital letter: Letters, suitable for diameters 3.0 ... 6.0 mm, yellow, mounting type: slide-on

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0800514:B     |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BG17          |
| Product key                          | BG222B        |
| GTIN                                 | 4017918490515 |
| Weight per piece (including packing) | 310 MGM       |
| Weight per piece (excluding packing) | 310 MGM       |
| Customs tariff number                | 49119900      |
| Country of origin                    | PL            |

# PMH 2:GROSSBUCHSTABEN B - Wire marking tag



0800514:B

<https://www.phoenixcontact.com/us/products/0800514:B>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|          |         |
|----------|---------|
| Printing | Letters |
|----------|---------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 4.2 mm  |
| Height | 9.5 mm  |
| Length | 6.60 mm |

### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 3 mm ... 6 mm |
|------------------|---------------|

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 4.20 mm |
| Text field height | 2.60 mm |

### Material specifications

|  |  |
|--|--|
| Color                                  | yellow (RAL 1018)                        |
| Material                               | Ethylene-vinyl acetate (EVA)             |
| Flammability rating according to UL 94 | V0                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

0800514:B

<https://www.phoenixcontact.com/us/products/0800514:B>

## Classifications

### ECLASS

ECLASS-13.0

27281102

### ETIM

ETIM 9.0

EC001530

### UNSPSC

UNSPSC 21.0

39131500

# PMH 2:GROSSBUCHSTABEN B - Wire marking tag



0800514:B

<https://www.phoenixcontact.com/us/products/0800514:B>

## Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) |  |
|-------------------------------------|--|
|-------------------------------------|--|

|  |                            |
|--|----------------------------|
|  | No substance above 0.1 wt% |
|--|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)