

PMH 4:UNBEDRUCKT - Wire marking tag



0800572

<https://www.phoenixcontact.com/us/products/0800572>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, yellow (RAL 1018), unmarked, cable diameter range: 8.5 ... 12 mm: without print, mounting type: slide-on, text field height: 4 mm, text field width: 6.2 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0800572 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BG17 |
| Product key | BG221B |
| GTIN | 4017918006136 |
| Weight per piece (including packing) | 0.77 g |
| Weight per piece (excluding packing) | 0.72 g |
| Customs tariff number | 39269097 |
| Country of origin | CZ |

0800572

<https://www.phoenixcontact.com/us/products/0800572>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|----------|---------------|
| Printing | without print |
|----------|---------------|

Dimensions

| | |
|--------|---------|
| Width | 6.2 mm |
| Height | 16.5 mm |
| Length | 11 mm |

Text field

| | |
|-------------------|--------|
| Text field width | 6.2 mm |
| Text field height | 4 mm |

Material specifications

| | |
|--|--|
| Color | yellow (RAL 1018) |
| Material | Ethylene-vinyl acetate (EVA) |
| Flammability rating according to UL 94 | V0 |
| Components | free from silicone, halogen, and cadmium |

Cable/line

| | |
|-------------------------|------------------|
| External cable diameter | 8.5 mm ... 12 mm |
|-------------------------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -45 °C ... 70 °C |
|---------------------------------|------------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

PMH 4:UNBEDRUCKT - Wire marking tag



0800572

<https://www.phoenixcontact.com/us/products/0800572>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
|-------------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

PMH 4:UNBEDRUCKT - Wire marking tag



0800572

<https://www.phoenixcontact.com/us/products/0800572>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com