

THERMOMARK-RIBBON 110-WMSU - Ink ribbon



0801358

<https://www.phoenixcontact.com/us/products/0801358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, For roll printer for printing product groups WMS..., WMS-2 HF..., and WMTB HF-HP, length: 300 m, roll length: 300 m, width: 110 mm, color: black

Commercial data

Item number	0801358
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4046356632836
Weight per piece (including packing)	316 g
Weight per piece (excluding packing)	319.2 g
Customs tariff number	96121010
Country of origin	US

THERMOMARK-RIBBON 110-WMSU - Ink ribbon



0801358

<https://www.phoenixcontact.com/us/products/0801358>

Technical data

Product properties

Product type	Ink ribbon
Scope of supply	Ink ribbon

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	110 mm
Length	300 m
Length of roll	300 m

Material specifications

Color	black (RAL 9005)
Material	Polyolefin-compatible ink coating

THERMOMARK-RIBBON 110-WMSU - Ink ribbon



0801358

<https://www.phoenixcontact.com/us/products/0801358>

Classifications

ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

ETIM

ETIM 10.0	EC001694
-----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

0801358

<https://www.phoenixcontact.com/us/products/0801358>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com