


ZBF 3,5,QR:FORTL.ZAHLEN 81-90 - Zack Marker strip, flat

0801407:0081

<https://www.phoenixcontact.com/us/products/0801407:0081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip flat, 10-section, vertically labeled with the consecutive numbers: 81 ... 90, white, for terminal block width: 3.5 mm, mounting type: latching

The figure shows the ZBF 3,5:UNBEDRUCKT, -LGS:FORTL.ZAHLEN, -QR:FORTL.ZAHLEN, and CUS versions

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0801407:0081 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG05 |
| Product key | BG2122 |
| GTIN | 4046356665292 |
| Weight per piece (including packing) | 0.46 g |
| Weight per piece (excluding packing) | 0.26 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

ZBF 3,5,QR:FORTL.ZAHLEN 81-90 - Zack Marker strip, flat



0801407:0081

<https://www.phoenixcontact.com/us/products/0801407:0081>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 3.5 mm |

Marking

| | |
|-----------|-----------|
| Printing | 81 ... 90 |
| Slot type | flat |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life | 2 years |

Dimensions

| | |
|--------|---------|
| Width | 3.5 mm |
| Height | 6.4 mm |
| Depth | 1.60 mm |
| Pitch | 3.5 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 3.50 mm |
| Text field height | 5.20 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

ZBF 3,5,QR:FORTL.ZAHLEN 81-90 - Zack Marker strip, flat



0801407:0081

<https://www.phoenixcontact.com/us/products/0801407:0081>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

ZBF 3,5,QR:FORTL.ZAHLEN 81-90 - Zack Marker strip, flat



0801407:0081

<https://www.phoenixcontact.com/us/products/0801407:0081>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com