

UCT-WMT (15X4) VT CUS - Conductor marker



0801536

<https://www.phoenixcontact.com/us/products/0801536>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Conductor marker, can be ordered: by sheet, violet (RAL 4005), labeled according to customer specifications, cable diameter range: 0.6 ... 50 mm, mounting type: insert, Number of individual labels: 50



Commercial data

Item number	0801536
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8128
GTIN	4046356682817
Weight per piece (including packing)	10.9 g
Weight per piece (excluding packing)	10.9 g
Country of origin	PL

UCT-WMT (15X4) VT CUS - Conductor marker



0801536

<https://www.phoenixcontact.com/us/products/0801536>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	50
Number of individual labels per row	10
Identification technology	Thermotransfer

Dimensions

Width	15 mm
Length	4 mm

Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Flammability rating according to UL 94	V0
Base element material	PC
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Cable/line

External cable diameter	0.6 mm ... 50 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Mounting

Mounting type	insert
---------------	--------

UCT-WMT (15X4) VT CUS - Conductor marker



0801536

<https://www.phoenixcontact.com/us/products/0801536>

Classifications

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

UCT-WMT (15X4) VT CUS - Conductor marker



0801536

<https://www.phoenixcontact.com/us/products/0801536>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com