

MARKING BOX FR FR - Thermal transfer printer set



0801590

<https://www.phoenixcontact.com/us/products/0801590>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printing set, consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x THERMOMARK CARD, Order No. 5146464, 1 x MARKING NOTEBOOK (without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL, country-specific keyboard version and operating system

Commercial data

Item number	0801590
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG1222
GTIN	4046356700856
Weight per piece (including packing)	20.5 kg
Weight per piece (excluding packing)	20.5 kg
Country of origin	DE

MARKING BOX FR FR - Thermal transfer printer set



0801590

<https://www.phoenixcontact.com/us/products/0801590>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print resolution	300 dpi
Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	785 mm
-------	--------

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	10 % ... 80 %

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com