

CES-SRG-BK-13 - Cable sleeve



0801616

<https://www.phoenixcontact.com/us/products/0801616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 12 mm ... 13 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

Product description

Slotted cable sleeve

Commercial data

Item number	0801616
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CCX
GTIN	4046356674720
Weight per piece (including packing)	6.46 g
Weight per piece (excluding packing)	6.46 g
Customs tariff number	40169997
Country of origin	TW

0801616


<https://www.phoenixcontact.com/us/products/0801616>

Technical data

Product properties

Product type	Cable sleeve
No. of conductors	1

Dimensions

Dimensional drawing	
Width	19.5 mm
Height	17 mm
Length	29.5 mm

Material specifications

Material	NBR
----------	-----

Cable/line

External cable diameter	1x 12 mm ... 13 mm
-------------------------	--------------------

Characteristics

Seal size	small
Design, Format	Round cable
Design, Cable seal	slotted

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C (static)


CES-SRG-BK-13 - Cable sleeve

0801616

<https://www.phoenixcontact.com/us/products/0801616>

Drawings

Dimensional drawing



Dimensional drawing

CES-SRG-BK-13 - Cable sleeve



0801616

<https://www.phoenixcontact.com/us/products/0801616>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801616>

DNV

Approval ID: TAE00003VJ

CES-SRG-BK-13 - Cable sleeve



0801616

<https://www.phoenixcontact.com/us/products/0801616>

Classifications

ECLASS

ECLASS-15.0	27144425
ECLASS-13.0	27144425

ETIM

ETIM 10.0	EC000451
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.373 kg CO2e
---------	---------------