

MARKING BOX IT IT - Thermal transfer printer set



0801745

<https://www.phoenixcontact.com/us/products/0801745>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printing set, consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x THERMOMARK CARD, Order No. 5146464, 1 x MARKING NOTEBOOK (without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL, country-specific keyboard version and operating system

Commercial data

Item number	0801745
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG1222
GTIN	4046356694919
Weight per piece (including packing)	16,720.87 g
Weight per piece (excluding packing)	14,920.8 g
Country of origin	DE

MARKING BOX IT IT - Thermal transfer printer set



0801745

<https://www.phoenixcontact.com/us/products/0801745>

Set consists of

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

THERMOMARK CARD - Thermal transfer printer

5146464

<https://www.phoenixcontact.com/us/products/5146464>



Thermal transfer printer for cards

MARKING BOX IT IT - Thermal transfer printer set

0801745

<https://www.phoenixcontact.com/us/products/0801745>



CLIP-PROJECT ADVANCED - Software

5146040

<https://www.phoenixcontact.com/us/products/5146040>



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

0801745

<https://www.phoenixcontact.com/us/products/0801745>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print resolution	300 dpi
Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	785 mm
-------	--------

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	10 % ... 80 %

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com