

# BLUEMARK MAG EM-M (49X15) - Magazine



0802738

<https://www.phoenixcontact.com/us/products/0802738>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine, length: 0.12 m, width: 76 mm, height: 120 mm, color: white



## Your advantages

- In conjunction with the BLUEMARK CLED printer, the magazine for accommodating EMP-AL... ensures printing with a high degree of positioning accuracy.

## Commercial data

Item number	0802738
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG121Z
GTIN	4046356845762
Weight per piece (including packing)	59.7 g
Weight per piece (excluding packing)	47.28 g
Customs tariff number	90179000
Country of origin	DE

# BLUEMARK MAG EM-M (49X15) - Magazine



0802738

<https://www.phoenixcontact.com/us/products/0802738>

## Technical data

### Product properties

Product type	Magazine
--------------	----------

### Dimensions

Width	76 mm
Height	120 mm
Depth	4 mm
Length	120 mm

### Material specifications

Color	white
Material	POM

0802738

<https://www.phoenixcontact.com/us/products/0802738>

## Classifications

### ECLASS

ECLASS-13.0	19140615
ECLASS-15.0	19140615

### ETIM

ETIM 10.0	EC001675
-----------	----------

### UNSPSC

UNSPSC 21.0	43211600
-------------	----------

0802738

<https://www.phoenixcontact.com/us/products/0802738>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)