

# UCT-PMP (90X38) VT - Insert label



0803132

<https://www.phoenixcontact.com/us/products/0803132>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, violet (RAL 4005), unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, TOPMARK NEO, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, Number of individual labels: 1



## Your advantages

- The UCT-PMP (90x38) system marking label is easy to mount and, if necessary, remove
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The markers, which are supplied in uniform sheets, can be marked quickly and easily using the BLUEMARK ID..., BLUEMARK CLED, TOPMARK LASER, or TOPMARK NEO
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all labels according to your requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0803132       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Product key                          | BG2617        |
| GTIN                                 | 4046356964920 |
| Weight per piece (including packing) | 11.41 g       |
| Weight per piece (excluding packing) | 11.41 g       |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Plant marker |
|--------------|--------------|

### Marking

|                                     |                                         |
|-------------------------------------|-----------------------------------------|
| Number of individual labels         | 1                                       |
| Number of individual labels per row | 1                                       |
| Identification technology           | UV LED technology, direct laser marking |

### Dimensions

|        |          |
|--------|----------|
| Width  | 90.00 mm |
| Height | 38.00 mm |
| Depth  | 1.15 mm  |

### Material specifications

|                                                                  |                                |
|------------------------------------------------------------------|--------------------------------|
| RoHS compliant                                                   | yes                            |
| Color                                                            | violet (RAL 4005)              |
| Flammability rating according to UL 94                           | V0                             |
| Base element material                                            | PC                             |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C                         |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3                    |
| Components                                                       | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 80 °C |
|---------------------------------|------------------|

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Wipe resistance of inscriptions

|                             |                                                |
|-----------------------------|------------------------------------------------|
| Specification               | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|                             | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed                                    |

# UCT-PMP (90X38) VT - Insert label



0803132

<https://www.phoenixcontact.com/us/products/0803132>

|                                                 |             |
|-------------------------------------------------|-------------|
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

## Mounting

|               |                             |
|---------------|-----------------------------|
| Mounting type | snapped into marker carrier |
|---------------|-----------------------------|

# UCT-PMP (90X38) VT - Insert label



0803132

<https://www.phoenixcontact.com/us/products/0803132>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UCT-PMP (90X38) VT - Insert label



0803132

<https://www.phoenixcontact.com/us/products/0803132>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)