TMP-RIBBON 110 GN 100 - Ink ribbon cartridge

0803380

https://www.phoenixcontact.com/us/products/0803380

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., roll length: 60 m, width: 110 mm, color: green (RAL 6021)

Commercial data

Item number	0803380
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4055626042190
Weight per piece (including packing)	214 g
Weight per piece (excluding packing)	167 g
Customs tariff number	96121010
Country of origin	FR

Technical data

Product properties

Product type	Ink ribbon

Marking

Identification technology	Thermal transfer

Dimensions

Width	110 mm
Length of roll	60 m

Material specifications

Color	green (RAL 6021)
Material	Polyester

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	30 %

Classifications

ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

ETIM

ETIM 10.0	EC001694

UNSPSC

UNSPSC 21.0	44103100

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com