

TOPMARK LASER RR - Retaining frame



0803434

<https://www.phoenixcontact.com/us/products/0803434>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

O-Ring holding down clamp



Commercial data

Item number	0803434
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BGS12Y
GTIN	4055626077888
Weight per piece (including packing)	7.2 g
Weight per piece (excluding packing)	7.2 g
Country of origin	Information on the country of origin is provided with the delivery.

TOPMARK LASER RR - Retaining frame



0803434

<https://www.phoenixcontact.com/us/products/0803434>

Technical data

Product properties

Product type	Printing system accessories
Thread type	pluggable

Dimensions

Height	3 mm
Diameter	25 mm

Internal dimensions

Internal diameter	25 mm
-------------------	-------

Material specifications

Material	EPDM
----------	------

TOPMARK LASER RR - Retaining frame



0803434

<https://www.phoenixcontact.com/us/products/0803434>

Classifications

ECLASS

ECLASS-13.0	19140192
ECLASS-15.0	19140192

ETIM

ETIM 10.0	EC001675
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TOPMARK LASER RR - Retaining frame



0803434

<https://www.phoenixcontact.com/us/products/0803434>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com