

SK 7,5/3,8:FORTL.ZAHLEN - Marker card



0804455

<https://www.phoenixcontact.com/us/products/0804455>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Sheet, white (RAL 9010), labeled, horizontal: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: adhesive, for terminal block width: 7.5 mm, Number of individual labels: 12, text field height: 3.8 mm, text field width: 7.5 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

Commercial data

Item number	0804455
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	NULL
Product key	BG2123
Weight per piece (including packing)	1.55 g
Weight per piece (excluding packing)	1.39 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Notes

Order information:	For labeling according to customer requirement, please select 0825127 product
--------------------	---

Product properties

Product type	Terminal marker
Pitch	7.5 mm

Marking

Number of individual labels	12
Number of marker strips	12
Printing direction	horizontal
Printing	consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100

Dimensions

Width	7.5 mm
Height	3.8 mm
Pitch	7.5 mm

Text field

Text field width	7.5 mm
Text field height	3.8 mm

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

SK 7,5/3,8:FORTL.ZAHLEN - Marker card



0804455

<https://www.phoenixcontact.com/us/products/0804455>

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

SK 7,5/3,8:FORTL.ZAHLEN - Marker card



0804455

<https://www.phoenixcontact.com/us/products/0804455>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0804455

<https://www.phoenixcontact.com/us/products/0804455>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com