

# SK 7,5/5:FORTL.ZAHLEN - Marker card



0804468

<https://www.phoenixcontact.com/us/products/0804468>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Sheet, white (RAL 9010), labeled, horizontal: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: adhesive, for terminal block width: 7.5 mm, Number of individual labels: 10, text field height: 5 mm, text field width: 7.5 mm

## Your advantages

- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

## Commercial data

|                                      |          |
|--------------------------------------|----------|
| Item number                          | 0804468  |
| Packing unit                         | 10 pc    |
| Minimum order quantity               | 10 pc    |
| Sales key                            | BG05     |
| Product key                          | BG2123   |
| Weight per piece (including packing) | 1.53 g   |
| Weight per piece (excluding packing) | 1.18 g   |
| Customs tariff number                | 49119900 |
| Country of origin                    | DE       |

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Order information: | For labeling according to customer requirement, please select 0825131 product |
|--------------------|---|

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch        | 7.5 mm          |

### Marking

|                             |  |
|-----------------------------|--|
| Number of individual labels | 10   |
| Number of marker strips     | 10   |
| Printing direction          | horizontal   |
| Printing                    | consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100 |

### Dimensions

|        |        |
|--------|--------|
| Width  | 7.5 mm |
| Height | 5 mm   |
| Pitch  | 7.5 mm |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 7.5 mm |
| Text field height | 5 mm   |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Foil strength         | 53 µm                          |
| Adhesive strength     | 20 µm                          |
| Adhesive              | Acrylic                        |
| Color                 | white (RAL 9010)               |
| Material              | Polyester                      |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### UV resistance

# SK 7,5/5:FORTL.ZAHLEN - Marker card



0804468

<https://www.phoenixcontact.com/us/products/0804468>

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |

## Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

0804468

<https://www.phoenixcontact.com/us/products/0804468>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# SK 7,5/5:FORTL.ZAHLEN - Marker card



0804468

<https://www.phoenixcontact.com/us/products/0804468>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)