

GBS 5-25X12 - Group marker label for terminal marking

0810588

<https://www.phoenixcontact.com/us/products/0810588>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Group marker label, snaps onto terminal center for screw, spring-cage and quick connection terminal blocks, labeled with a 25 x 12 mm label or manually with the B-STIFT, in the foot part with ZB 5

Your advantages

- Fits all terminal blocks with tall center marker groove
- Large-surface marking with labels or manually using B-STIFT or X-PEN
- Space-saving group marking directly on the terminal block

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0810588 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BG12 |
| Product key | BG211A |
| GTIN | 4017918859152 |
| Weight per piece (including packing) | 0.967 g |
| Weight per piece (excluding packing) | 0.94 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

GBS 5-25X12 - Group marker label for terminal marking



0810588

<https://www.phoenixcontact.com/us/products/0810588>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 5.2 mm |

Dimensions

| | |
|--------|----------|
| Width | 14.00 mm |
| Height | 28.05 mm |
| Depth | 23.30 mm |
| Pitch | 5.2 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 25 mm |
| Text field height | 12 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

GBS 5-25X12 - Group marker label for terminal marking



0810588

<https://www.phoenixcontact.com/us/products/0810588>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

GBS 5-25X12 - Group marker label for terminal marking



0810588

<https://www.phoenixcontact.com/us/products/0810588>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.011 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com