

# BMKLT 41,5X12 WH - Label sheet, DIN A4



0813815

<https://www.phoenixcontact.com/us/products/0813815>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 88



## Your advantages

- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0813815                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BG13                           |
| Product key                          | BG2414                         |
| GTIN                                 | 4017918966935                  |
| Weight per piece (including packing) | 20.67 g                        |
| Weight per piece (excluding packing) | 20.67 g                        |
| Customs tariff number                | 39199080                       |
| Country of origin                    | DE                             |

0813815

<https://www.phoenixcontact.com/us/products/0813815>

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                                     |    |
|-------------------------------------|----|
| Number of individual labels         | 88 |
| Number of individual labels per row | 4  |

### Dimensions

|        |         |
|--------|---------|
| Width  | 41.5 mm |
| Length | 12 mm   |

### Material specifications

|                       |               |
|-----------------------|---------------|
| Color                 | white         |
| Material              | Polyester     |
| Base element material | Polyester     |
| Components            | Silicone-free |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# BMKLT 41,5X12 WH - Label sheet, DIN A4



0813815

<https://www.phoenixcontact.com/us/products/0813815>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)