

PATO 1/18 - Conductor marker carrier



0823740

<https://www.phoenixcontact.com/us/products/0823740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, unmarked, cable diameter range: 2 ... 3.5 mm, mounting type: clip on, text field height: 4 mm, text field width: 18 mm

Your advantages

- Can be labeled using UC-WMT ... or US-WMT ... plastic labels or the EMT ... insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0823740 |
| Packing unit | 500 pc |
| Minimum order quantity | 500 pc |
| Sales key | BG12 |
| Product key | BG221A |
| GTIN | 4046356333658 |
| Weight per piece (including packing) | 0.42 g |
| Weight per piece (excluding packing) | 0.38 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

0823740

<https://www.phoenixcontact.com/us/products/0823740>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|--------|
| Width | 18 mm |
| Height | 5.6 mm |
| Depth | 8.2 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 18 mm |
| Text field height | 4 mm |

Material specifications

| | |
|--|---------------|
| Color | transparent |
| Material | PVC |
| Flammability rating according to UL 94 | V0 |
| Base element material | PVC |
| Components | Silicone-free |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 2 mm ... 3.5 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -50 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|---------|
| Mounting type | clip on |
|---------------|---------|

PATO 1/18 - Conductor marker carrier



0823740

<https://www.phoenixcontact.com/us/products/0823740>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PATO 1/18 - Conductor marker carrier



0823740

<https://www.phoenixcontact.com/us/products/0823740>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.003 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com