

# BMKL 12X12 WH CUS - Label sheet, DIN A4



0824238

<https://www.phoenixcontact.com/us/products/0824238>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, can be ordered: in sheets, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 273, text field height: 12 mm, text field width: 12 mm



## Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The unperforated SK-U... sheets are available for custom label designs

## Commercial data

Item number	0824238
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8144
GTIN	4046356351133
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	9 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	273
Number of individual labels per row	13
Identification technology	Office laser printing

### Dimensions

Width	12.00 mm
Height	12.00 mm
Depth	0.09 mm
Length	12 mm

### Text field

Text field width	12 mm
Text field height	12 mm

### Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	adhesive
---------------	----------

0824238

<https://www.phoenixcontact.com/us/products/0824238>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# BMKL 12X12 WH CUS - Label sheet, DIN A4



0824238

<https://www.phoenixcontact.com/us/products/0824238>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)