

BMKL 18X 8 YE CUS - Label sheet, DIN A4




0824245

<https://www.phoenixcontact.com/us/products/0824245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, can be ordered: in sheets, yellow (RAL 1018), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 288, text field height: 8 mm, text field width: 18 mm



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The unperforated SK-U... sheets are available for custom label designs

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0824245 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8144 |
| GTIN | 4046356351201 |
| Weight per piece (including packing) | 12.2 g |
| Weight per piece (excluding packing) | 9 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|-------------------------------------|-----------------------|
| Number of individual labels | 288 |
| Number of individual labels per row | 9 |
| Identification technology | Office laser printing |

Dimensions

| | |
|--------|----------|
| Width | 8.00 mm |
| Height | 18.00 mm |
| Depth | 0.09 mm |
| Length | 8 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 18 mm |
| Text field height | 8 mm |

Material specifications

| | |
|-----------------------|-------------------|
| Color | yellow (RAL 1018) |
| Material | Polyester |
| Base element material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -20 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

0824245

<https://www.phoenixcontact.com/us/products/0824245>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

BMKL 18X 8 YE CUS - Label sheet, DIN A4



0824245

<https://www.phoenixcontact.com/us/products/0824245>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com