

SD-WMS 3 (CH) YE:O - Wire marking tag



0825557:O

<https://www.phoenixcontact.com/us/products/0825557:O>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the capital letter: Letters, yellow, the dimensions of the replacement product differ from the previous product!, mounting type: thread on

Commercial data

Item number	0825557:O
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG17
Product key	BG222B
GTIN	4046356415293
Weight per piece (including packing)	31.6 MGM
Weight per piece (excluding packing)	31.6 MGM
Customs tariff number	49119900
Country of origin	SE

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing	Letters
Slot type	Profile

Dimensions

Width	3.2 mm
Height	3.6 mm
Length	3.50 mm

External dimensions

Outside diameter	1.3 mm ... 3 mm
------------------	-----------------

Material specifications

Color	yellow
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	thread on
---------------	-----------

SD-WMS 3 (CH) YE:O - Wire marking tag



0825557:O

<https://www.phoenixcontact.com/us/products/0825557:O>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com