

SD-WMS 10 (SY) - Wire marking tag

0826187

<https://www.phoenixcontact.com/us/products/0826187>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, cable diameter range: 4 ... 10 mm, horizontal: Symbols, mounting type: thread on

The figure shows the article SD-WMS 10 (CH) YE

Commercial data

Item number	0826187
Packing unit	1 pc
Sales key	BG17
Product key	BG222B
Weight per piece (including packing)	333 g
Weight per piece (excluding packing)	333 g
Customs tariff number	49119900
Country of origin	SE

SD-WMS 10 (SY) - Wire marking tag



0826187

<https://www.phoenixcontact.com/us/products/0826187>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing direction	horizontal
Printing	Symbols
Slot type	Profile

Dimensions

Width	4.2 mm
Height	9.5 mm
Length	6.6 mm

Material specifications

Color	white
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

Cable/line

External cable diameter	4 mm ... 10 mm
-------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	thread on
---------------	-----------

SD-WMS 10 (SY) - Wire marking tag



0826187

<https://www.phoenixcontact.com/us/products/0826187>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com