

UC-WMC 3,1 (15X4) VT CUS - Conductor marker



0826773

<https://www.phoenixcontact.com/us/products/0826773>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Conductor marker, can be ordered: by sheet, violet (RAL 4005), labeled according to customer specifications, cable diameter range: 1.9 ... 3.1 mm, mounting type: clip on, Number of individual labels: 20



Your advantages

- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- The markers support multi-line labeling
- One-handed mounting
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- Two labeling areas that are clearly legible at all times
- Can be clipped on even after wiring has been completed

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0826773 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8127 |
| GTIN | 4046356364089 |
| Weight per piece (including packing) | 11.58 g |
| Weight per piece (excluding packing) | 8.7 g |
| Country of origin | PL |

UC-WMC 3,1 (15X4) VT CUS - Conductor marker



0826773

<https://www.phoenixcontact.com/us/products/0826773>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|-------------------|
| Number of individual labels | 20 |
| Number of individual labels per row | 4 |
| Slot type | Card form |
| Identification technology | UV LED technology |

Dimensions

| | |
|--------|-------|
| Width | 4 mm |
| Length | 15 mm |

Material specifications

| | |
|---|--------------------------------|
| RoHS compliant | yes |
| Color | violet (RAL 4005) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 120 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2 |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|-------------------|
| External cable diameter | 1.9 mm ... 3.1 mm |
|-------------------------|-------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

UC-WMC 3,1 (15X4) VT CUS - Conductor marker



0826773

<https://www.phoenixcontact.com/us/products/0826773>

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|---------|
| Mounting type | clip on |
|---------------|---------|

UC-WMC 3,1 (15X4) VT CUS - Conductor marker



0826773

<https://www.phoenixcontact.com/us/products/0826773>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

UC-WMC 3,1 (15X4) VT CUS - Conductor marker



0826773

<https://www.phoenixcontact.com/us/products/0826773>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com