

# KMV CUS - Stainless steel label



0828493

<https://www.phoenixcontact.com/us/products/0828493>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stainless steel label, Stainless steel label, can be ordered: Piece, labeled according to customer specifications, cable diameter range: 1 ... 63 mm, mounting type: Assembly with cable ties, Number of individual labels: 1, text field height: 19 mm, text field width: 65 mm

## Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

## Commercial data

Item number	0828493
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8145
GTIN	4046356512640
Weight per piece (including packing)	3.07 g
Weight per piece (excluding packing)	3 g
Customs tariff number	73269098
Country of origin	PL

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	1
Slot type	Mounting set

### Dimensions

Width	19.00 mm
Height	89.00 mm
Depth	0.90 mm
Length	89 mm

### Text field

Text field width	65 mm
Text field height	19 mm

### Material specifications

Color	silver-colored
Material	Stainless steel 304
Base element material	Stainless steel

### Cable/line

External cable diameter	1 mm ... 63 mm
-------------------------	----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# KMV CUS - Stainless steel label



0828493

<https://www.phoenixcontact.com/us/products/0828493>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# KMV CUS - Stainless steel label



0828493

<https://www.phoenixcontact.com/us/products/0828493>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)