

# PABA WH/18 - Cable marker



0829427

<https://www.phoenixcontact.com/us/products/0829427>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Strip, white (RAL 9010), unmarked, can be labeled with: CMS-P1-PLOTTER, cable diameter range: 0.6 ... 22 mm, mounting type: slide-on, Number of individual labels: 1, text field height: 4 mm, text field width: 18 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0829427       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BG20          |
| Product key                          | BG2213        |
| GTIN                                 | 4046356559232 |
| Weight per piece (including packing) | 6.47 g        |
| Weight per piece (excluding packing) | 4.5 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | CN            |

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|                             |   |
|-----------------------------|---|
| Number of individual labels | 1 |
|-----------------------------|---|

### Dimensions

|        |         |
|--------|---------|
| Width  | 17.9 mm |
| Height | 4 mm    |
| Depth  | 1.85 mm |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 18 mm |
| Text field height | 4 mm  |

### Material specifications

|                       |                  |
|-----------------------|------------------|
| Color                 | white (RAL 9010) |
| Material              | PA               |
| Base element material | PA               |

### Cable/line

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 0.6 mm ... 22 mm |
|-------------------------|------------------|

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)                     | -15 °C ... 65 °C |
| Recommended ambient temperature (storage/transport) | 23 °C            |
| Recommended humidity (storage/transport)            | 50 %             |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |

#### Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# PABA WH/18 - Cable marker



0829427

<https://www.phoenixcontact.com/us/products/0829427>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# PABA WH/18 - Cable marker



0829427

<https://www.phoenixcontact.com/us/products/0829427>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)