

THERMOMARK-RIBBON 110 BU - Ink ribbon



0829544

<https://www.phoenixcontact.com/us/products/0829544>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0829544 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG02 |
| Product key | BG1223 |
| GTIN | 4046356608787 |
| Weight per piece (including packing) | 350 g |
| Weight per piece (excluding packing) | 311.6 g |
| Customs tariff number | 96121010 |
| Country of origin | FR |

THERMOMARK-RIBBON 110 BU - Ink ribbon



0829544

<https://www.phoenixcontact.com/us/products/0829544>

Technical data

Product properties

| | |
|--------------|------------|
| Product type | Ink ribbon |
|--------------|------------|

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|--------|
| Width | 110 mm |
| Length | 300 m |
| Length of roll | 300 m |

Material specifications

| | |
|-------|-----------------|
| Color | blue (RAL 5015) |
|-------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------|
| Recommended ambient temperature (storage/transport) | 5 °C |
| Recommended humidity (storage/transport) | 20 % |

THERMOMARK-RIBBON 110 BU - Ink ribbon



0829544

<https://www.phoenixcontact.com/us/products/0829544>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19140614 |
| ECLASS-15.0 | 19140614 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001694 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 44103100 |
|-------------|----------|

THERMOMARK-RIBBON 110 BU - Ink ribbon



0829544

<https://www.phoenixcontact.com/us/products/0829544>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com