ZB 20,3 AXL UNPRINTED - Zack marker strip

0829579

https://www.phoenixcontact.com/us/products/0829579

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip for Axioline F (device labeling), in 2 x 20.3 mm pitch, unprinted, 25-section, for individual labeling with B-STIFT 0.8, X-PEN, or CMS-P1-PLOTTER

Commercial data

Item number	0829579
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	NULL
Product key	BG2112
GTIN	4046356591249
Weight per piece (including packing)	0.89 g
Weight per piece (excluding packing)	0.89 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Terminal marker
Pitch	20.3 mm

Marking

Number of individual labels	25
Number of individual labels per row	5
Number of marker strips	5
Slot type	high

Dimensions

Width	20.25 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	20.3 mm

Text field

Text field width	10.5 mm
Text field height	10.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	latching

Classifications

ECLASS

ECLASS-13.0	27281101

ETIM

ETIM 9.0	EC000761

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.008 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com