# E PX A 405X400X121 - Empty enclosure

0899322

https://www.phoenixcontact.com/us/products/0899322

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a similar product

Empty enclosure, material: Glass-fiber-reinforced polyester with added graphite, black, 405 mm x 400 mm x 121 mm, type of locking: Screw-on cover

## Commercial data

| | |
|---|---|
| Item number | 0899322 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BH91 |
| Product key | BH9142 |
| GTIN | 4055626275918 |
| Weight per piece (including packing) | 99.99 g |
| Weight per piece (excluding packing) | 99.99 g |
| Customs tariff number | 85389099 |
| Country of origin | IN |

## Technical data

### Notes

| | |
|---|---|
| General | Prepared for direct installation of a DIN rail |


### Product properties

| | |
|---|---|
| Product type | Terminal box |
| Type | Ex empty enclosure with cover |

Insulation characteristics

| | |
|---|---|
| Protection class | II |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 405 mm |
| Height | 400 mm |
| Depth | 121 mm |
| Clearance width, maximum DIN rail length | 381 mm |
| max. assembly length | 362 mm |

### Material specifications

| | |
|---|---|
| Color | black |
| Material | Glass-fiber-reinforced polyester with added graphite |
| Flammability rating according to UL 94 | V0 |
| Seal material | Silicon |
| Components | halogen-free |

### Mechanical properties

General

| | |
|---|---|
| Type of locking (GRP) | Screw-on cover Plus/minus screw |

### Environmental and real-life conditions

Degree of protection (IP code)

| | |
|---|---|
| Degree of protection | IP66 |

Ambient conditions


| | |
|---|---|
| Ambient temperature (operation) | -55 °C ... 127 °C |

### Mounting


| | |
|---|---|
| Assembly note | External fixing clips available as an option |
| | Integrated blind hole |
| Direct DIN rail mounting | yes |
| Useable DIN rail type | NS 35 |

## Drawings

Dimensional drawing




Schematic diagram



## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27180101 |
| ECLASS-15.0 | 27180101 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000261 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com