

TMC 1 M1 100 7,0A - Thermal-magnetic device circuit breaker



0915474

<https://www.phoenixcontact.com/us/products/0915474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic circuit breaker, 1-pos., normal blow, 1 N/O contact, with universal foot for mounting on NS 32 or NS 35

Commercial data

Item number	0915474
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	CL04
Product key	CLA121
GTIN	4046356338585
Weight per piece (including packing)	77.77 g
Weight per piece (excluding packing)	77.77 g
Customs tariff number	85362010
Country of origin	DE

TMC 1 M1 100 7,0A - Thermal-magnetic device circuit breaker



0915474

<https://www.phoenixcontact.com/us/products/0915474>

Technical data

Product properties

Product type	Thermomagnetic device circuit breakers
Product family	TMC
Type	DIN rail module, one-piece
Number of positions	1

Electrical properties

Fuse type	Automatic device
Fuse	M1 (normal blow)

General

Tripping method	TM (thermal-magnetic)
Fuse	M1 (normal blow)
Contact switching type	1 N/O contact

Connection data

Nominal current	7 A
Nominal voltage	250 V AC
	65 V DC

Dimensions

Width	12.5 mm
Height	83.5 mm
Depth	96 mm

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

TMC 1 M1 100 7,0A - Thermal-magnetic device circuit breaker



0915474

<https://www.phoenixcontact.com/us/products/0915474>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com