

1004856

<https://www.phoenixcontact.com/us/products/1004856>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a combination of versions A/F, A/U, VAH, A/F-HA

Flat-ribbon cover, for covering terminal strips, 2 mm thick, 3 cm wide, an additional requirement are 2 E/UK end brackets and 2 adjustable VAH cover holders. The max. supply length is 100 cm

Commercial data

Item number	1004856
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH84
Product key	BH8412
GTIN	4017918012243
Weight per piece (including packing)	90 g
Weight per piece (excluding packing)	90 g
Customs tariff number	39206100
Country of origin	DE

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	30 mm
Length	1 m

Material specifications

Color	transparent
Material	Polycarbonate PC
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

1004856

<https://www.phoenixcontact.com/us/products/1004856>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141192

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.989 kg CO2e
---------	---------------