

1004869

<https://www.phoenixcontact.com/us/products/1004869>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a combination of versions A/F, A/U, VAH, A/F-HA

Flat-ribbon cover, for covering terminal strips, 2 mm thick, 2,0 cm wide, an additional requirement are 2 E/UK end brackets and 2 adjustable VAH cover holders. The max. supply length is 100 cm

## Commercial data

Item number	1004869
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH84
Product key	BH8412
GTIN	4017918012250
Weight per piece (including packing)	60 g
Weight per piece (excluding packing)	60 g
Customs tariff number	39206100
Country of origin	DE

## Technical data

### Product properties

Product type	Cover profile
--------------	---------------

### Dimensions

Width	20 mm
Length	1 m

### Material specifications

Color	transparent
Material	Polycarbonate PC
Flammability rating according to UL 94	V2

1004869

<https://www.phoenixcontact.com/us/products/1004869>

### Classifications

#### ECLASS

ECLASS-15.0	27141192
ECLASS-13.0	27141190

#### ETIM

ETIM 10.0	EC002848
-----------	----------

#### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------