

# PKB 190X4,8 BK - Cable tie



1005538

<https://www.phoenixcontact.com/us/products/1005538>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable tie, resistant to UV rays, dimensions: L x W, 190 x 4.8 mm, color: black

## Commercial data

Item number	1005538
Packing unit	1,000 pc
Sales key	BE07
Product key	BE7131
GTIN	4017918012601
Weight per piece (including packing)	1.24 g
Weight per piece (excluding packing)	1.24 g
Customs tariff number	39269097
Country of origin	SG

# PKB 190X4,8 BK - Cable tie



1005538

<https://www.phoenixcontact.com/us/products/1005538>

## Technical data

### Product properties

Product type	Cable tie
Tensile strength GRP	220 N

### Dimensions

Width	4.8 mm
Length	190 mm

### Material specifications

Color	black
Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

### Cable/line

Tensile strength	220 N
------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	yes

### Mounting

Mounting type	Cannot be removed
---------------	-------------------

# PKB 190X4,8 BK - Cable tie



1005538

<https://www.phoenixcontact.com/us/products/1005538>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)