

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

Product description

Robust connecting cable Q-ODC-24 to Q-ODC-24, push-pull interlocking, degree of protection: IP68

Your advantages

- Compact design with MT ferrule
- Push-pull interlocking
- For extreme ambient conditions

Commercial data

Item number	1007809
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNHAA
GTIN	4055626480763
Weight per piece (including packing)	1,760 g
Weight per piece (excluding packing)	1,740 g
Country of origin	CN

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	24

Electrical properties

Attenuation	typ. 0.15 dB
	max. 0.35 dB
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	500 N
---------------------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSFH

Connector

Connection 1

Degree of protection	IP68
	IP68

Connection 2

Degree of protection	IP68
----------------------	------

Cable/line

Cable length	100 m
Cable weight	55.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Outer sheath, material	LSFH
External sheath, color	black
Tensile strength short-term/long-term	500 N
Halogen-free	complying with IEC 60754-1/2

FO cable

Number of fibers	24
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

FOC-OP24-OP24-GL03/100 - Connecting cable



1007809

<https://www.phoenixcontact.com/us/products/1007809>

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	50g, in accordance with IEC 61300-2-9

FOC-OP24-OP24-GL03/100 - Connecting cable



1007809

<https://www.phoenixcontact.com/us/products/1007809>

Classifications

ECLASS

ECLASS-13.0	27061003
-------------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%