

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/us/products/1013425>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 6 A, contact connection type: Socket, connection method: Crimp connection, contact surface: Gold, type of packaging: Bulk goods, product range: MCC 0,5-MP

Commercial data

Item number	1013425
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AA01
Product key	AAACAB
GTIN	4055626492414
Weight per piece (including packing)	0.469 g
Weight per piece (excluding packing)	0.064 g
Customs tariff number	85366990
Country of origin	CZ

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/us/products/1013425>

Technical data

Product properties

Product type	Crimp contact
Product family	MCC 0,5-MP
Pitch	0 mm

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Stripping length	4.1 mm ... 4.5 mm
Conductor cross-section flexible	0.14 mm ² ... 0.5 mm ²
Conductor cross-section AWG	26 ... 20

Material specifications

Contact surface	Gold Au
Contact surface material	Gold
Metal surface terminal point (top layer)	Tin (3 - 6 µm Sn)
Metal surface contact area (top layer)	Gold (0.25 Au)
Surface characteristics	Selective coating
Contact material	Cu alloy

Dimensions

Pitch	-
-------	---

Electrical properties

Nominal current I _N	6 A
--------------------------------	-----

Packaging specifications

Type of packaging	Bulk goods
-------------------	------------

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/us/products/1013425>

Classifications

ECLASS

ECLASS-13.0	27460403
ECLASS-15.0	27460403

ETIM

ETIM 10.0	EC000796
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

MCC 0,5-MP AU 0,14-0,5 - Crimp contact



1013425

<https://www.phoenixcontact.com/us/products/1013425>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com