

PML-GHS105 (13X13) - Hazardous substances label



1014277

<https://www.phoenixcontact.com/us/products/1014277>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hazardous substances label, Sheet, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 35, text field height: 13 mm, text field width: 13 mm

Your advantages

- High adhesive strength
- High temperature resistance
- Stick-on hazardous substances labels, preprinted with symbol
- The markers conform to the GHS international standard
- Suitable for indoor and outdoor use

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1014277 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Product key | BG2624 |
| GTIN | 4046356786942 |
| Weight per piece (including packing) | 5.7 g |
| Weight per piece (excluding packing) | 1 g |
| Country of origin | DE |

PML-GHS105 (13X13) - Hazardous substances label



1014277

<https://www.phoenixcontact.com/us/products/1014277>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Plant marker |
| Area of application | Hazardous substance labels |
| | Hazardous substance labeling according to CLP/GHS regulation |
| Type | Diamond |

Marking

| | |
|-----------------------------|-----------|
| Number of individual labels | 35 |
| Printing | Corrosive |

Dimensions

| | |
|--------|-------|
| Width | 13 mm |
| Height | 13 mm |
| Length | 13 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 13 mm |
| Text field height | 13 mm |

Material specifications

| | |
|------------|---------------|
| Color | red/white |
| Material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

PML-GHS105 (13X13) - Hazardous substances label



1014277

<https://www.phoenixcontact.com/us/products/1014277>

Classifications

ECLASS

ECLASS-13.0

40200202

ETIM

ETIM 9.0

EC001777

UNSPSC

UNSPSC 21.0

55121700

PML-GHS105 (13X13) - Hazardous substances label



1014277

<https://www.phoenixcontact.com/us/products/1014277>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com