


PMM (EX40)R SR CUS - Magnetic label



1014328

<https://www.phoenixcontact.com/us/products/1014328>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Magnetic label, Roll, can be ordered: by line, labeled according to customer specifications, mounting type: magnetic adhesion, Number of individual labels: 1, text field height: 40 mm, text field width: 15000 mm

Commercial data

Item number	1014328
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8151
GTIN	4046356786324
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

PMM (EX40)R SR CUS - Magnetic label



1014328

<https://www.phoenixcontact.com/us/products/1014328>

Technical data

Product properties

Product type	Plant marker
Area of application	Warehousing/logistics
Product property	magnetic

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	50.00 mm
Height	40.00 mm
Depth	0.60 mm
Length	15000 mm

Text field

Text field width	15000 mm
Text field height	40 mm

Material specifications

Color	silver-colored
Material	Magnetic tape
Coating	Polyester foil
Base element material	Magnetic tape

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

PMM (EX40)R SR CUS - Magnetic label



1014328

<https://www.phoenixcontact.com/us/products/1014328>

Mounting

Mounting type	magnetic adhesion
---------------	-------------------

PMM (EX40)R SR CUS - Magnetic label



1014328

<https://www.phoenixcontact.com/us/products/1014328>

Classifications

ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PMM (EX40)R SR CUS - Magnetic label



1014328
<https://www.phoenixcontact.com/us/products/1014328>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com