

NBC-MSX/20,0-94S/FSX-8QO SCO - Network cable



1015953

<https://www.phoenixcontact.com/us/products/1015953>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT6_A (10 Gbps), 8-position, shielded, Plug straight M12 SPEEDCON, coding: X / IP67, on 1414586 SACC-FSX-8QO SH ETH SCO, cable length: 20 m

Commercial data

Item number	1015953
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1CMJ
GTIN	4055626497716
Weight per piece (including packing)	1,258.3 g
Weight per piece (excluding packing)	1,258.3 g
Customs tariff number	85444290
Country of origin	PL

1015953

<https://www.phoenixcontact.com/us/products/1015953>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	8

Interfaces

Signal type/category	Ethernet CAT6 _A , 10 Gbps
----------------------	--------------------------------------

Electrical properties

Nominal voltage U _N	48 V AC
	60 V DC
Transmission speed	10 Gbps

Material specifications

Outer sheath, material	PUR
------------------------	-----

Connector

Connection 1

Type	Plug straight M12 SPEEDCON / IP67
Number of positions	8
Locking type	SPEEDCON
Coding type	X (Data)
Handle color	black
Material	CuZn (Contact)
	Ni/Au (Contact surface)
	PP (Contact carrier)
	TPU, hardly inflammable, self-extinguishing (Grip body) Zinc die-cast, nickel-plated (Screw connection)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C

Connection 2

Type	1414586 SACC-FSX-8QO SH ETH SCO
------	---------------------------------

Cable/line

Cable length	20 m
Signal type/category	Ethernet CAT6 _A , 10 Gbps
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021

NBC-MSX/20,0-94S/FSX-8QO SCO - Network cable



1015953

<https://www.phoenixcontact.com/us/products/1015953>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1015953

<https://www.phoenixcontact.com/us/products/1015953>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com