

SAC-3P-0,33-PUR/M5FS - Sensor/actuator cable



1016385

<https://www.phoenixcontact.com/us/products/1016385>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR, black RAL 9005, free cable end, on Socket straight M5, coding: A, cable length: 0.33 m

Commercial data

Item number	1016385
Packing unit	1 pc
Minimum order quantity	100 pc
Product key	AF1ABA
GTIN	4055626498515
Weight per piece (including packing)	9.9 g
Weight per piece (excluding packing)	9.9 g
Country of origin	DE

SAC-3P-0,33-PUR/M5FS - Sensor/actuator cable



1016385

<https://www.phoenixcontact.com/us/products/1016385>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Socket straight M5
Number of positions	3
Coding type	A

Cable/line

Cable length	0.33 m
--------------	--------

PUR/PVC black [350]

Dimensional drawing	
Cable weight	12.9 kg/km
Number of positions	3
Shielded	no
Cable type	PUR/PVC black [350]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross-section	3x 0.14 mm ² (Signal line)
Wire diameter incl. insulation	1.1 mm
External cable diameter	3.00 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC

SAC-3P-0,33-PUR/M5FS - Sensor/actuator cable



1016385

<https://www.phoenixcontact.com/us/products/1016385>

Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Max. conductor resistance	148 Ω /km
Insulation resistance	100 $M\Omega$ *km
Nominal voltage, cable	250 V
Test voltage	800 V_{rms}
Smallest bending radius, fixed installation	8 mm
Smallest bending radius, movable installation	15 mm
Ambient temperature (operation)	-15 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-0,33-PUR/M5FS - Sensor/actuator cable



1016385

<https://www.phoenixcontact.com/us/products/1016385>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com