

1024085

<https://www.phoenixcontact.com/us/products/1024085>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single covers, for covering one terminal block, with black symbol (lightning flash) snap fit, color: transparent/yellow



## Your advantages

- Can be labeled
- Protection against accidental actuation of terminal points or disconnect terminal blocks
- Covering of live parts

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1024085       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE07          |
| Product key                          | BE7124        |
| GTIN                                 | 4017918015275 |
| Weight per piece (including packing) | 0.874 g       |
| Weight per piece (excluding packing) | 0.852 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Cover profile |
|--------------|---------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 5 mm    |
| Height | 50 mm   |
| Depth  | 17.5 mm |
| Length | 50 mm   |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | yellow (RAL 1018)              |
| Material                               | ABS                            |
| Flammability rating according to UL 94 | HB                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

1024085

<https://www.phoenixcontact.com/us/products/1024085>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
| ECLASS-15.0 | 27281107 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)