

# ME MAX B-22,5 RD S75 - Filler plug

1030270

<https://www.phoenixcontact.com/us/products/1030270>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug with vents for unoccupied terminal points, width: 20 mm, height: 21.6 mm, depth: 8.1 mm, color: red (similar RAL 3001)

The figure shows a version of the product

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	1030270
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4055626533582
Weight per piece (including packing)	0.992 g
Weight per piece (excluding packing)	0.992 g
Country of origin	DE

# ME MAX B-22,5 RD S75 - Filler plug



1030270

<https://www.phoenixcontact.com/us/products/1030270>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 22,5..
Ventilation openings present	no

### Dimensions

Width	20 mm
Height	21.6 mm
Depth	8.1 mm

### Material specifications

Color (Housing)	red (RAL 3001)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

### Packaging specifications

Outer packaging type	Resealable bag
----------------------	----------------

# ME MAX B-22,5 RD S75 - Filler plug



1030270

<https://www.phoenixcontact.com/us/products/1030270>

## Classifications

### ECLASS

ECLASS-13.0

27190605

### ETIM

ETIM 9.0

EC002779

### UNSPSC

UNSPSC 21.0

31261500

# ME MAX B-22,5 RD S75 - Filler plug



1030270

<https://www.phoenixcontact.com/us/products/1030270>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.042 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)