

# HSCP-CB 6U-7035 - Fastening clip

1037100

<https://www.phoenixcontact.com/us/products/1037100>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ME-IO Blockbelt, for 6 PCB connectors, Blockbelt, width: 8.1 mm, height: 65.7 mm, depth: 1.25 mm, color: light gray (similar RAL 7035)

## Your advantages

- Enables the functional grouping of various connector plugs
- Simplifies service and maintenance work
- Fast mounting and removal of the clamps through a latch system

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1037100       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | AC15          |
| Product key                          | ACHECZ        |
| GTIN                                 | 4055626570044 |
| Weight per piece (including packing) | 0.64 g        |
| Weight per piece (excluding packing) | 0.64 g        |
| Customs tariff number                | 85389099      |
| Country of origin                    | PL            |

# HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

## Technical data

### Product properties

|                |                   |
|----------------|-------------------|
| Product type   | Mounting material |
| Housing type   | ME-IO Blockbelt   |
| Housing series | ME-IO             |
| Product family | ME-IO             |

### Dimensions

|        |         |
|--------|---------|
| Width  | 8.1 mm  |
| Height | 65.7 mm |
| Depth  | 1.25 mm |

### Material specifications

|  |                       |
|--|-----------------------|
| Color                                  | light gray (RAL 7035) |
| Material                               | PA                    |
| Flammability rating according to UL 94 | V0                    |
| Surface characteristics                | untreated             |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

# HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HSCP-CB 6U-7035 - Fastening clip



1037100

<https://www.phoenixcontact.com/us/products/1037100>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)