

BM ID-DUMMY CARTR. CY - Ink cartridge



1044352

<https://www.phoenixcontact.com/us/products/1044352>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Dummy cartridge for transportation, color: cyan



Commercial data

Item number	1044352
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG121Z
GTIN	4055626622439
Weight per piece (including packing)	111.7 g
Weight per piece (excluding packing)	111 g
Customs tariff number	84439990
Country of origin	DE

BM ID-DUMMY CARTR. CY - Ink cartridge



1044352

<https://www.phoenixcontact.com/us/products/1044352>

Technical data

Environmental and real-life conditions

Ambient conditions

Recommended storage conditions	0°C ... 20°C, cool and dry storage in the original packaging is recommended.
--------------------------------	--

BM ID-DUMMY CARTR. CY - Ink cartridge



1044352

<https://www.phoenixcontact.com/us/products/1044352>

Classifications

ECLASS

ECLASS-13.0	19140192
ECLASS-15.0	19140192

ETIM

ETIM 10.0	EC001675
-----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

BM ID-DUMMY CARTR. CY - Ink cartridge



1044352

<https://www.phoenixcontact.com/us/products/1044352>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com