

BM ID-MAG40 - Magazine



1044357

<https://www.phoenixcontact.com/us/products/1044357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Infeed magazine for accommodating a maxi. of 40 UniCard sheets



Commercial data

Item number	1044357
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG121Z
GTIN	4055626622583
Weight per piece (including packing)	1,090 g
Weight per piece (excluding packing)	1,076 g
Customs tariff number	84439990
Country of origin	DE

Technical data

Product properties

Product type	Magazine
--------------	----------

Material specifications

RoHS compliant	yes
----------------	-----

Environmental and real-life conditions

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

1044357

<https://www.phoenixcontact.com/us/products/1044357>

Classifications

ECLASS

ECLASS-13.0	19140192
ECLASS-15.0	19140192

ETIM

ETIM 10.0	EC001675
-----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

1044357

<https://www.phoenixcontact.com/us/products/1044357>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com